



# OC-S-63

63-1/4" x 39-3/8" Vikrell® roll-in shower with Aging in Place backerboards, center drain  
62060106



### Features

- 1/2" (12.7 mm) threshold
- Durable swirl-gloss finish
- Three-piece tongue-and-groove walls with snap-together installation
- Aging in Place backerboards
- Modular design allows it to be moved around corners and through doorways with ease

### Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty

### Installation

- Alcove
- Center drain
- Caulk required for proper installation

### Recommended Products/Accessories

- K-23726 Drain treatment
- K-23733 Vikrell® cleaner

### Included Components

- 62065106 39-3/8" Vikrell® shower end wall set with Aging in Place backerboards
- 62061100 63-1/2" x 39-3/8" Vikrell® roll-in shower base, center drain, center drain
- 62062106 63-1/4" Vikrell® shower back wall with Aging in Place backerboards



### Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662
- HUD, UM Bulletin 73

### STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty


See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

#### Color Code Description

	0	White
-------------------------------------------------------------------------------------	---	-------



**Technical Information**

All product dimensions are nominal.

Drain location: Center

**Notes**

Install this product according to the installation instructions.

Attach grab bars at the specified backerboard locations only.

1/2" minimum finished floor thickness required.

Studs should be positioned as shown.

Drain cutout in subfloor to be 10-1/2" (267 mm) per rough-in illustration as shown to allow the backside of the drain to sit below the subflow surface.

Backerboards and fasteners protrude beyond the back wall 1-1/2" (38 mm). If installing this product against wall board, 1-1/2" (38 mm) furring strips installed over the wall board are recommended. The stud pocket depth of 40-5/8" (1032 mm) will need to be increased by the combined thickness of the wall board and furring strips.