











DETAIL A
ENGINE EXHAUST OUTLET
SCALE 0.12




DETAIL B
OPTIONAL FLEX
EXHAUST FLANGE
SCALE 0.12




NOTE:
DIMENSIONS IN [] ARE INCH EQUIVALENTS
IF IBC CERTIFICATION IS REQUIRED, SEE SEISMIC ADV FOR INSTALLATION INSTRUCTIONS.

1250 MODEL 50/60 HZ
7M4046, 7M4048, 7M4050, 7M4052, 7M4172,
7M4174, 7M4288, 7M4366, 7M4368
RECONNECTABLE
380V, 600V, 4160V ALTERNATORS
40C & 50C COOLING SYSTEM
MITSUBISHI, TIER I

REV	DATE	ON COMPOSITE DWGS, SEE PART NO. FOR REVISION LEVEL	BY	DO NOT SCALE. REFERENCE THE MODEL FOR ALL UNSPECIFIED DIMENSIONS		
-	4-26-11	NEW DRAWING [91304-3]	DJV	UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS IN MILLIMETERS GENERAL TOLERANCES: N/A	KOHLER KOHLER, WISCONSIN 53044 THIS DRAWING IN DESIGN AND DETAIL IS KOHLER CO. PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH KOHLER CO. WORK. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED.	TITLE DIMENSION PRINT, 1250ROZMC
A	5-19-11	SEE SHEET 1 [91691]	KJB			
B	2-9-12	SEE SHEET 1 & 3 [CT05336]	CEK			
C	4-27-19	(B-4) 2282 [89.9] WAS 2221 [87.5]; (C-7) 4291 [168.9] WAS 4261 [167.7]; (A-2) 371 [14.6] WAS 348 [13.7]; (C-2) 2128 [83.8] WAS 2311 [91.0]; (B-2) HEAVY DUTY CLEANERS ORIENTATION CHANGED & VIEW UPDATED; SEE SHEET 1, 3, 4 & 5 [CT195448]	PAR			
D	8-20-19	(A-4) 1250 MODEL 50/60 HZ WAS 1250 MODEL 60 HZ; SEE SHEET 1, 3, 4 & 5 [CT197994]	RRT	THIRD ANGLE PROJECTION 	APPROVALS DRAWN DJV CHECKED DJV APPROVED WRD	DATE 4-26-11 4-26-11 4-26-11
				SCALE 0.06 CAD NO. SHEET 2 of 5 DWG NO. ADV-8175 D		






3/4" N.P.T FUEL
INLET CONNECTION

FUEL RETURN

OPTIONAL FUEL INLET AND RETURN LOCATIONS



FUEL/WATER
SEPARATOR

FUEL AND WATER SEPARATOR

1250 MODEL 50/60 HZ
7M4046, 7M4048, 7M4050, 7M4052, 7M4172,
7M4174, 7M4288, 7M4366, 7M4368
RECONNECTABLE
380V, 600V, 4160V ALTERNATORS
40C & 50C COOLING SYSTEM
MITSUBISHI, TIER I

NOTE:
DIMENSIONS IN [] ARE INCH EQUIVALENTS
IF IBC CERTIFICATION IS REQUIRED, SEE SEISMIC ADV FOR INSTALLATION INSTRUCTIONS.

REV

DATE

ON COMPOSITE DWGS. SEE PART NO. FOR REVISION LEVEL

BY

-

4-26-11

NEW DRAWING [91304-3]

DJV

A

5-19-11

SEE SHEET 1 [91691]

KJB

B

2-9-12

SEE SHEET 1 & 3 [CT05336]

CEK

C

4-27-19

(A-6) 2641 [104.0] WAS 2432 [95.8], 388 [15.3]
WAS 425 [16.7]; (C-5) 371 [14.6] WAS 348 [13.7];
SEE SHEET 1, 2, 3 & 4 [CT195448]

PAR

D

8-20-19

(A-4) 1250 MODEL 50/60 HZ WAS 1250 MODEL 60 HZ;
SEE SHEET 1, 2, 3 & 4 [CT197994]

RRT

DO NOT SCALE. REFERENCE THE MODEL FOR ALL UNSPECIFIED DIMENSIONS

UNLESS OTHERWISE SPECIFIED:
ALL DIMENSIONS IN MILLIMETERS
GENERAL TOLERANCES: N/A

THIRD ANGLE PROJECTION



APPROVALS

DATE

DRAWN

DJV

4-26-11

CHECKED

DJV

4-26-11

APPROVED

WRD

4-26-11

KOHLER.

KOHLER, WISCONSIN 53044

THIS DRAWING IN DESIGN AND DETAIL IS KOHLER CO. PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH KOHLER CO. WORK. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED.

TITLE

DIMENSION PRINT, 1250ROZMC

SCALE

0.08

CAD NO.

SHEET

5

of

5

DWG NO.

ADV-8175

D