



LEFT SIDE ONLY WHEN
BREAKERS OR LOAD BUS
ARE PRESENT ON LEFT SIDE



208-600V
KD1250-1750KW 60HZ

1250-1750 KW				
ALTERNATOR FRAME SIZE				
	KH04830TO4D	KH05520TO4D	KH03850TO4D KH04590TO4D KH04920TO4D	KH05740TO4D KH06400TO4D KH06810TO4D
A	5204 [204.9]	5284 [208.0]	5239 [206.3]	5469 [215.3]

1250-1750 KW				
COG WITH RESPECT TO DIFFERENT ALTERNATORS - 9 SECTION RADIATOR				
MODEL	ALT.	GENSET MAXIMUM WEIGHT (WET)	HORIZONTAL CG (WET)	VERTICAL CG (WET)
KD1250	KH04830TO4D	11039 [24346 lbs]	2828 [111.3]	845 [33.3]
KD1250	KH05520TO4D	11352 [25037 lbs]	2879 [113.3]	846 [33.3]
KD1250/1500	KH03850TO4D	11417 [25179 lbs]	2851 [112.2]	846 [33.3]
KD1250/1500	KH04590TO4D	11816 [26061 lbs]	2917 [114.8]	847 [33.3]
KD1500	KH04920TO4D	12016 [26501 lbs]	2944 [115.9]	848 [33.4]
KD1500	KH05740TO4D	12281 [27085 lbs]	2997 [118.0]	848 [33.4]
KD1750	KH06400TO4D	12767 [28157 lbs]	3057 [120.4]	849 [33.4]
KD1250/1500	KH06810TO4D	12896 [28443 lbs]	3077 [121.1]	850 [33.5]

COG WITH RESPECT TO DIFFERENT ALTERNATORS - 10 SECTION RADIATOR				
KD1600	KH04590TO4D	12043 [26561 lbs]	2890 [113.8]	846 [33.3]
KD1600/1750	KH04920TO4D	12243 [27002 lbs]	2917 [114.8]	846 [33.3]
KD1600/1750	KH05740TO4D	12508 [27585 lbs]	2970 [116.9]	847 [33.3]
KD1750	KH06400TO4D	12994 [28657 lbs]	3029 [119.3]	848 [33.4]
KD1600/1750	KH06810TO4D	13123 [28943 lbs]	3049 [120.0]	848 [33.4]

DIMENSIONS	1250/1500 KW 50°C 1600/1750 KW 40°C RADIATOR	1600/1750KW 50°C RADIATOR
B	2480 [97.6]	2580 [101.6]
C	2152 [84.7]	2382 [93.8]
D	2022 [79.6]	2247 [88.5]
E	1894 [74.5]	2000 [78.7]
F	1977 [77.8]	2207 [86.9]

- NOTES:
- 1) DIMENSIONS IN [] ARE ENGLISH EQUIVALENTS.
 - 2) IF AN ENCLOSURE IS USED THE FUEL LINE MUST BE STUBBED UP FROM DIRECTLY UNDER THE UNIT. REFER TO ENCLOSURE ADV.
 - 3) IF IBC OR OSHPD CERTIFICATION IS REQUIRED SEE SEISMIC ADV FOR INSTALLATION INSTRUCTIONS.
 - 4) IF SUBBASE FUEL TANK AND/OR ENCLOSURE IS USED. REFER TO SUBBASE FUEL TANK/ENCLOSURE ADV TO DETERMINE MOUNTING LOCATION.

REV	DATE	ON COMPOSITE DWGS, SEE PART NO. FOR REVISION LEVEL	BY	DO NOT SCALE. REFERENCE THE MODEL FOR ALL UNSPECIFIED DIMENSIONS			
E	8-20-18	SHEET 8 ADDED, SEE SHEET 3 [CT189948]	SSS	UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS IN MILLIMETERS GENERAL TOLERANCES: X.XX ± X.X ± X ANGLES ± SURFACE FINISH MAX. THIRD ANGLE PROJECTION			
F	23APR2020	(C-1,2) "1250/1500 KW 50°C 1600/1750 KW 40°C RADIATOR" WAS "1250/1500 KW 50°C RADIATOR"; SEE SHEET 7 [CT203726]	YBY				
G	19MAY2020	(B-8) CIRCUIT BREAKER BOX CALLOUT ADDED; SEE SHEET 4 [CT204162]	PAR	APPROVALS DRAWN ADP 8-19-16 CHECKED CEK 8-19-16 APPROVED TAS 8-19-16			
H	20AUG2021	(A, B-8) ALTERNATOR UPDATED; (A-6) "A" DIMENSION UPDATED [CT214160]	RVM				
				TITLE DIMENSION PRINT, KD1250-1750KW			
				SCALE 0.40 CAD NO. SHEET 1 of 8			
				ADV-8899 D			



5799 [228.3]

847	[33.3
-----	--------

846 [33.3]

4) IF SUBBASE FUEL TANK AND/OR ENCLOSURE IS USED. REFER TO SUBBASE FUEL TANK/ENCLOSURE ADV TO DETERMINE MOUNTING LOCATION.







DETAIL B
SCALE 0.30

APPROVED	TAS	8-19-16	ADV-8899
----------	-----	---------	----------



KD1250-1750KW 60HZ

8		7		6		5		4		3		2		1	
GENSET MODEL		ALTERNATOR		GENSET MAX WEIGHT (WET)		HORIZONTAL CG (WET) "X" MEASURED FROM FRONT OF GENSET		VERTICAL CG (WET) "Z" MEASURED FROM BOTTOM OF SKID		"A" (FRONT OF SKID TO REAR PANEL OF ALTERNATOR)					
KD1500		KH03850TO4D		10310 [22729 lbs]		3110 [122.4]		794 [31.3]		5240 [206.3]					
KD1500/KD1600		KH04590TO4D		10709 [23610 lbs]		3173 [124.9]		798 [31.4]		5240 [206.3]					
KD1500/KD1600/KD1750		KH04920TO4D		10909 [24051 lbs]		3198 [125.9]		799 [31.5]		5240 [206.3]					
KD1500/KD1600/KD1750		KH05740TO4D		11051 [24364 lbs]		3250 [128.0]		801 [31.5]		5469 [215.3]					
KD1750		KH06400TO4D		11660 [25706 lbs]		3305 [130.1]		804 [31.7]		5469 [215.3]					
KD1500/KD1600/KD1750		KH06810TO4D		11790 [25992 lbs]		3324 [130.9]		805 [31.7]		5469 [215.3]					
KD1500/KD1600/KD1750		KH05641TO4D		11015 [24285 lbs]		3274 [128.9]		798 [31.4]		5700 [224.4]					
KD1500/KD1600/KD1750		KH06721TO4D		11425 [25188 lbs]		3340 [131.5]		801 [31.5]		5799 [228.3]					



DIMENSIONS IN [] ARE INCH EQUIVALENTS





SCALE 0.03



REV	DATE	ON COMPOSITE DWGS. SEE PART NO. FOR REVISION LEVEL	BY	DO NOT SCALE. REFERENCE THE MODEL FOR ALL UNSPECIFIED DIMENSIONS	
E	8-20-18	REMOTE RADIATOR SETUP ADDED & CONTENTS OF THIS SHEET MOVED TO SHEET 4 [CT189948]	SSS	UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS IN MILLIMETERS GENERAL TOLERANCES: X, XX ± 0.25 X, Y ± 1.0 SURFACE FINISH X ± 1.5 MAX. ANGLES ± 0°30' THIRD ANGLE PROJECTION KOHLER. KOHLER, WISCONSIN 53044 THIS DRAWING IN DESIGN AND DETAIL IS KOHLER CO. PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH KOHLER CO. WORK. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED. TITLE DIMENSION PRINT, KD1250-1750KW SCALE 0.06 CAD NO. SHEET 3 of 8 DWG NO. ADV-8899	
F	23APR2020	SEE SHEET 1 & 7 [CT203726]	YBY		
G	19MAY2020	SEE SHEET 1 & 4 [CT204162]	PAR		
H	20AUG2021	SEE SHEET 1 [CT214160]	RVM		
		APPROVALS	DATE		
		DRAWN ADP	8-17-18		
		CHECKED CEK	8-17-18		
		APPROVED TAS	8-17-18		





* GENERATOR LIFT POINTS
TO BE USED TO LIFT
OPEN GENERATOR ONLY





KD1250-1750KW 50/60HZ

REV	DATE	ON COMPOSITE DWGS, SEE PART NO. FOR REVISION LEVEL	BY	DO NOT SCALE. REFERENCE THE MODEL FOR ALL UNSPECIFIED DIMENSIONS			
C	8-14-17	SEE SHEET 5 [CT174085]	CEK	UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS IN MILLIMETERS GENERAL TOLERANCES: X.XX ± X.X ± X ± ANGLES ± SURFACE FINISH MAX. THIRD ANGLE PROJECTION			
D	12-22-17	(B-4) 1615.5 [63.60] ADDED & Ø 251 [9.88] REMOVED, (C-8) 2227 [87.68] & (C-4) 1590 [62.60] ADDED, SEE SHEET 1 & 5 [CT182881]	YBY				
E	8-20-18	CONTENT OF SHEET 3 MOVED TO SHEET 4 & CONTENT OF SHEET 4 MOVED TO SHEET 5 [CT189948]	SSS				
F	23APR2020	SEE SHEET 1 & 7 [CT203726]	YBY	APPROVALS DRAWN ADP 8-19-16 CHECKED CEK 8-19-16 APPROVED TAS 8-19-16			
G	19MAY2020	(A-5) CONTROLLER CALLOUT ADDED; SEE SHEET 1 [CT204162]	PAR				
H	20AUG2021	SEE SHEET 1 [CT214160]	RVM				
				TITLE DIMENSION PRINT, KD1250-1750KW SCALE 0.40 CAD NO. SHEET 4 of 8 DWG NO. ADV-8899			











BASIC ELECTRICAL PACKAGE (BEP) LOAD CENTER



ALTERNATOR AIR FILTER INSTALLED
INSIDE OF LOUVERED PANELS
(7% DERATE ON GENERATOR RATING)

ALTERNATOR HEATER THREADS
INTO REAR CASTING OF ALTERNATOR

ALTERNATOR AIR FILTER & HEATER



AIR RESTRICTION GAUGE

AIR FILTER RESTRICTION INDICATOR
(LEFT SIDE OF GENSET)

KD1250-1750KW 50/60HZ

REV	DATE	ON COMPOSITE DWGS. SEE PART NO. FOR REVISION LEVEL	BY	DO NOT SCALE. REFERENCE THE MODEL FOR ALL UNSPECIFIED DIMENSIONS			
-	8-19-16	NEW DRAWING [CT153994]	ADP	UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS IN MILLIMETERS GENERAL TOLERANCES: X.XX ± X.X ± X ± ANGLES ± SURFACE FINISH MAX. THIRD ANGLE PROJECTION			
A	11-21-16	SEE SHEET 1 & 6 [166235]	CEK				
B	5-3-17	(A-6) REGENERATE VIEW [CT174085]	CEK				
C	8-14-17	SEE SHEET 5 [CT174085]	CEK				
D	12-22-17	SEE SHEET 1, 3 & 5 [CT182881]	YBY				
E	8-20-18	CONTENT OF SHEET 7 MOVED TO SHEET 8 [CT189948]	SSS	TITLE KOHLER. KOHLER, WISCONSIN 53044 THIS DRAWING IN DESIGN AND DETAIL IS KOHLER CO. PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH KOHLER CO. WORK. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED. DIMENSION PRINT, KD1250-1750KW SCALE 0.40 CAD NO. SHEET 8 of 8 DWG NO. ADV-8899			
F	23APR2020	SEE SHEET 1 & 7 [CT203726]	YBY				
G	19MAY2020	SEE SHEET 1 & 4 [CT204162]	PAR				
H	20AUG2021	SEE SHEET 1 [CT214160]	RVM				
			APPROVED	TAS	8-19-16		