



	4UA9, 4UA13 mm [IN]	4R13X, 4S12X, 4T13X, 4S13X mm [IN]
A	500 [19.7]	400 [15.7]
B	302 [11.9]	400 [15.7]
C	315 [12.4]	300 [11.8]
D	100 [3.9]	150 [5.9]
E	1376 [54.2]	1244 [49.0]
F	50 [2.0]	311 [12.2]

NOTES:
 1. IF ENCLOSURE IS INSTALLED, REFER TO ENCLOSURE ADV.
 2. IF IBC CERTIFICATION IS REQUIRED SEE SEISMIC ADV FOR INSTALLATION INSTRUCTIONS.
 NOTE: DIMENSIONS IN [] ARE ENGLISH EQUIVALENTS.

MODEL	ALTERNATOR	GENSET MAX WEIGHT kg (lb)	HORIZONTAL CG mm [IN]	VERTICAL CG mm [IN]
KG150	4R13X	1420 [3135]	1410 [55.5]	600 [23.5]
KG150	4T13X	1420 [3135]	1410 [55.5]	600 [23.5]
KG150 / KG180	4S12X	1460 [3225]	1380 [54.3]	585 [23.0]
KG150 / KG180 / KG200	4S13X	1500 [3310]	1350 [53.3]	585 [23.0]
KG200	4UA9	1850 [4085]	1230 [48.5]	555 [21.8]
KG180 / KG200	4UA13	2030 [4480]	1155 [45.5]	555 [21.8]

* WOOD BASE IS AN ADDITIONAL 120 kg [265 lb]






KG150-200 MODEL, 4R13X, 4S12X, 4S13X, 4T13X
 KG180-200 MODEL, 4UA9, 4UA13
 RECONNECTABLE AND 600V ALTERNATORS




REV	DATE	ON COMPOSITE DWGS, SEE PART NO. FOR REVISION LEVEL	BY	DO NOT SCALE, REFERENCE THE MODEL FOR ALL UNSPECIFIED DIMENSIONS
-	3-19-20	NEW DRAWING [CT202736]	PAS	UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS IN MILLIMETERS GENERAL TOLERANCES: N/A
A	7-14-21	(D-7) DIM 1154 ADDED, DIM 250 ADDED; (D-8) DIM 80 ADDED, DIM 395 ADDED [CT213319]	WHA	
B	28OCT2021	SEE SHEET 2 [CT215755]	SAK	

THIRD ANGLE PROJECTION	
APPROVALS	DATE
DRWN PAS	3-19-20
CHEK DJV	3-19-20
APPR WDG	3-19-20

TITLE		DIMENSION PRINT, KG150-200	
SCALE 0.11	CAD NO.	SHEET 1 of 3	
DWG NO. ADV-9045		D	




OPTIONAL RADIATOR DUCT FLANGE AND STONE GUARD




SCALE 0.38
EXHAUST OUTLET
ASME B16.5 NPS 4
DETAIL A

KG150-200 MODEL, 4R13X, 4S12X, 4S13X, 4T13X
KG180-200 MODEL, 4UA9, 4UA13
RECONNECTABLE AND 600V ALTERNATORS


REV	DATE	ON COMPOSITE DWGS, SEE PART NO. FOR REVISION LEVEL	BY	DO NOT SCALE, REFERENCE THE MODEL FOR ALL UNSPECIFIED DIMENSIONS
-	3-19-20	NEW DRAWING [CT202736]	PAS	UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS IN MILLIMETERS GENERAL TOLERANCES: N/A
A	7-14-21	SEE SHEET 1 [CT213319]	WHA	
B	28OCT2021	VIEWS UPDATED TO SHOW FLEX EXHAUST, (B-8)2330 ADDED, (C-8) 465 ADDED [CT215755]	SAK	
THIRD ANGLE PROJECTION				
		APPROVALS	DATE	KOHLER KOHLER, WISCONSIN 53044 THIS DRAWING IN DESIGN AND DETAIL IS KOHLER CO. PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH KOHLER CO. WORK. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED. TITLE DIMENSION PRINT, KG150-200 SCALE 0.09 CAD NO. SHEET 2 of 3 DWG NO. ADV-9045
		DRAWN	PAS 3-19-20	
		CHECKED	DJV 3-19-20	
		APPROVED	WDG 3-19-20	




DUAL FUEL OPTION
(RIGHT SIDE OF GENSET)
KG180/200 WITH 4UA SHOWN




BATTERY CHARGER
(RIGHT SIDE OF GENSET)




BASIC ELECTRICAL PACKAGE
SCALE 0.25
VIEW OF FRONT OF JUNCTION BOX
FROM FRONT OF GENSET



STANDARD DUTY AIR CLEANER
(RIGHT SIDE OF GENSET)



AIR RESTRICTION INDICATOR
AIR FILTER



BLOCK HEATER
(LEFT SIDE OF GENSET)

REV	DATE	ON COMPOSITE DWGS. SEE PART NO. FOR REVISION LEVEL	BY	DO NOT SCALE. REFERENCE THE MODEL FOR ALL UNSPECIFIED DIMENSIONS								
-	3-19-20	NEW DRAWING [CT202736]	PAS	UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS IN MILLIMETERS GENERAL TOLERANCES: N/A								
A	7-14-21	SEE SHEET 1 [CT213319]	WHA									
B	28OCT2021	SEE SHEET 2 [CT215755]	SAK									
				<table border="1"> <tr> <th colspan="2">THIRD ANGLE PROJECTION</th> </tr> <tr> <td></td> <td></td> </tr> </table>	THIRD ANGLE PROJECTION							
THIRD ANGLE PROJECTION												
				<table border="1"> <tr> <th>APPROVALS</th> <th>DATE</th> </tr> <tr> <td>DRAWN PAS</td> <td>3-19-20</td> </tr> <tr> <td>CHECKED DJV</td> <td>3-19-20</td> </tr> <tr> <td>APPROVED WDG</td> <td>3-19-20</td> </tr> </table>	APPROVALS	DATE	DRAWN PAS	3-19-20	CHECKED DJV	3-19-20	APPROVED WDG	3-19-20
APPROVALS	DATE											
DRAWN PAS	3-19-20											
CHECKED DJV	3-19-20											
APPROVED WDG	3-19-20											
				<p>KOHLER KOHLER, WISCONSIN 53044 THIS DRAWING IN DESIGN AND DETAIL IS KOHLER CO. PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH KOHLER CO. WORK. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED.</p> <p>TITLE: DIMENSION PRINT, KG150-200</p> <p>SCALE 0.11 CAD NO. SHEET 3 of 3</p> <p>DWG NO. ADV-9045</p>								