







TANK INFORMATION					
LITERS [GALLONS]	MIN HOURS	GENSETS	DIM A MM [INCH]	DIM B MM [INCH]	TANK WEIGHT KG [LBS] (NO FUEL)
1530 [404]	12 HOURS	350-400KW	406.4 [16.0]	5760.8[226.8]	1110 [2446]
1771 [468]	12 HOURS	500KW	457.2 [18.0]	5760.8[226.8]	1158 [2554]
2930 [774]	24 HOURS	350-400KW	762.0 [30.0]	5760.8[226.8]	1401 [3089]
3384 [894]	24 HOURS	500KW	838.2 [33.0]	5760.8[226.8]	1484 [3271]
4394 [1161]	36 HOURS	350-400KW	914.4 [36.0]	6459.8[254.3]	1789 [3945]
5047 [1333]	36 HOURS	500KW	914.4 [36.0]	7094.8[279.3]	1986 [4379]
1530 [404]	12 HOURS STATE	350-400KW	381.0 [15.0]	6713.8[264.3]	1299 [2864]
1771 [468]	12 HOURS STATE	500KW	431.8 [17.0]	6713.8[264.3]	1333 [2939]
2930 [774]	24 HOURS STATE	350-400KW	660.4 [26.0]	6713.8[264.3]	1547 [3411]
3384 [894]	24 HOURS STATE	500KW	736.6 [29.0]	6713.8[264.3]	1630 [3594]
4394 [1161]	36 HOURS STATE	350-400KW	914.4 [36.0]	6891.6[271.3]	1847 [4072]
5047 [1333]	36 HOURS STATE	500KW	914.4 [36.0]	7653.6[301.3]	2094 [4616]

350-500KW REOZJC/D
STEEL & ALUMINUM ENCL.
12 - 36 HOUR TANKS


350-500 REOZJC/D			KG [LBS]	
STEEL SOUND L2 ENCLOSURE WEIGHT			1000 [2205] APPROX	
ALUM. SOUND L2 ENCLOSURE WEIGHT			590 [1300] APPROX	
STEEL SOUND L1 ENCLOSURE WEIGHT			870 [1920] APPROX	
ALUM. SOUND L1 ENCLOSURE WEIGHT			460 [1015] APPROX	
STEEL WEATHER ENCLOSURE WEIGHT			850 [1875] APPROX	
REV	DATE	ON COMPOSITE DWGS. SEE PART NO. FOR REVISION LEVEL	BY	DO NOT SCALE. REFERENCE THE MODEL FOR ALL UNSPECIFIED DIMENSIONS
-	25NOV2019	NEW DRAWING [CT200393]	YBY	THIRD ANGLE PROJECTION APPROVALS DATE DRAWN YBY 25NOV2019 CHECKED KJB 25NOV2019 APPROVED DMS 25NOV2019
A	17AUG2021	SEE SHEET 6 & 7 [CT214138]	RNN	
B	1NOV2021	SHEET 8 ADDED; SEE SHEET 7 & 8 [CT215771]	SAK	
C	14DEC2021	SHEET 9 & 10 ADDED [CT216616]	MVT	
				KOHLER. KOHLER, WISCONSIN 53044 THIS DRAWING IN DESIGN AND DETAIL IS KOHLER CO. PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH KOHLER CO. WORK. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED. TITLE DIMENSION PRINT, 350-500REOZJC/D ENCL & TANKS SCALE 0.05 CAD NO. SHEET of 10 DWG NO. ADV-9189 D







8		7		6		5		4		3		2		1	
TANK INFORMATION															
LITERS [GALLONS] MIN HOURS		GENSETS	DIM A MM [INCH]	DIM B MM [INCH]	M	N	P	Q	R	S	T	V	W	X	
1530 [404] 12 HOURS		350-400KW	406.4 [16.0]	5760.8 [226.8]	66.3 [2.61]	606.8 [23.89]	488.5 [19.23]	961.7 [37.86]	937.9 [36.93]	482.6 [19.00]	668.6 [26.32]	931.5 [36.67]	931.5 [36.67]	523.9 [20.63]	
1771 [468] 12 HOURS		500KW	457.2 [18.0]	5760.8 [226.8]											
2930 [774] 24 HOURS		350-400KW	762.0 [30.0]	5760.8 [226.8]											
3384 [894] 24 HOURS		500KW	838.2 [33.0]	5760.8 [226.8]											
4394 [1161] 36 HOURS		350-400KW	914.4 [36.0]	6459.8 [254.3]											
5047 [1333] 36 HOURS		500KW	914.4 [36.0]	7094.8 [279.3]									574.6 [22.62]	648.3 [25.52]	
1530 [404] 12 HOURS STATE		350-400KW	381.0 [15.0]	6713.8 [264.3]									577.0 [22.72]	576.6 [22.70]	
1771 [468] 12 HOURS STATE		500KW	431.8 [17.0]	6713.8 [264.3]									664.2 [26.15]	812.7 [32.00]	
2930 [774] 24 HOURS STATE		350-400KW	660.4 [26.0]	6713.8 [264.3]											
3384 [894] 24 HOURS STATE		500KW	736.6 [29.0]	6713.8 [264.3]											
4394 [1161] 36 HOURS STATE		350-400KW	914.4 [36.0]	6891.6 [271.3]	704.3 [27.73]	772.6 [30.42]									
5047 [1333] 36 HOURS STATE		500KW	914.4 [36.0]	7653.6 [301.3]	891.3 [35.09]	821.1 [32.33]									




4396 [1161 GAL.] 36 HOUR STATE TANK SHOWN.

9	FILL CAP, 2" LOCKABLE W/PIPE RISER
8	SWITCH, FUEL IN BASIN TOP MTD, 2"
7	VENT, NORMAL
6	GAUGE, FUEL LEVEL, DIRECT READ
5	RETURN, FUEL (3/4" NPT)
4	SUPPLY, FUEL (1/2" NPT)
3	GAUGE, FUEL LEVEL, W/ SENDER
2	PLUG, PIPE (2" NPT)
1	CAP, EMERGENCY VENT
ITEM	DESCRIPTION

REV	DATE	ON COMPOSITE DWGS, SEE PART NO. FOR REVISION LEVEL	BY	DO NOT SCALE. REFERENCE THE MODEL FOR ALL UNSPECIFIED DIMENSIONS					
-	25NOV2019	NEW DRAWING [CT200393]	YBY	THIRD ANGLE PROJECTION 		KOHLER. KOHLER, WISCONSIN 53044 THIS DRAWING IN DESIGN AND DETAIL IS KOHLER CO. PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH KOHLER CO. WORK. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED. TITLE DIMENSION PRINT, 350-500RE0ZJC/D ENCL & TANKS			
A	17AUG2021	(C-8) 20X Ø25.4 [1.00] ADDED, SEE SHEET 7 [CT214138]	RNN						
B	1NOV2021	SEE SHEET 7 & 8 [CT215771]	SAK						
C	14DEC2021	SEE SHEET 1, 9 & 10 [CT216616]	MVT						
				APPROVALS		DATE			
				DRAWN	YBY	25NOV2019			
				CHECKED	KJB	25NOV2019			
				APPROVED	DMS	25NOV2019			
				SCALE		0.08	CAD NO.	SHEET	of 10
				DWG NO.		ADV-9189			D

8		7		6		5		4		3		2		1					
TANK INFORMATION																			
LITERS [GALLONS] MIN HOURS	GENSETS	DIM A MM [INCH]	DIM B MM [INCH]	DIM C MM [INCH]	DIM D MM [INCH]	TANK WEIGHT KG [LBS] (NO FUEL)	M	N	P	Q	R	S	T	U	V	W	X	Y	
7510 [1984] 72 HOURS	350KW	762.0 [30.0]	5850.1 [230.3]	2590.8 [102.0]	1120.9 [44.13]	3486 [7686]	305.8 [12.0]	595.1 [23.4]	575.0 [22.6]	649.5 [25.6]	804.0 [31.7]	616.5 [24.3]	800.1 [31.5]	515.0 [20.3]	518.3 [20.4]	-	-	-	
8695 [2297] 72 HOURS	400KW	889.0 [35.0]	5850.1 [230.3]			3656 [8061]													
9971 [2634] 72 HOURS	500KW	914.4 [36.0]	6028.0 [237.3]			3901 [8600]													
7537 [1991] 72 HOURS STATE	350KW	660.4 [26.0]	6282.0 [247.3]			3263 [7193]													
8748 [2311] 72 HOURS STATE	400KW	762.0 [30.0]	6282.0 [247.3]			3415 [7529]													
9993 [2640] 72 HOURS STATE	500KW	863.6 [34.0]	6282.0 [247.3]			4063 [8958]													
9993 [2640] 96 HOURS STATE	350KW		6282.0 [247.3]			4063 [8958]													
11602 [3065] 96 HOURS STATE	400KW		7264.4 [286.0]			4426 [9758]													
13325 [3520] 96 HOURS STATE	500KW		8305.8 [327.0]													4863 [10720]			
																	907.2 [35.7]	589.2 [23.2]	



[illegible]