

KDxxxx designates a generator set with a Tier 2 EPA-Certified engine. KDxxxx-F designates a 60 Hz generator set with a fuel optimized engine.

## **Ratings Range**

 60 Hz

 Standby:
 kW
 670-750

 kVA
 835-935

 Prime:
 kW
 600-680

 kVA
 750-850



## **Standard Features**

- Kohler Co. provides one-source responsibility for the generating system and accessories.
- Approved for use with certified renewable Hydrotreated Vegetable Oil (HVO) / Renewable Diesel (RD) fuels compliant with EN15940 / ASTM D975.
- The generator set and its components are prototype-tested, factory-built, and production-tested.
- cULus listing (UL 2200 and CSA C22.2 No. 100).
- The generator set accepts rated load in one step.
- The 60 Hz generator set meets NFPA 110, Level 1, when equipped with the necessary accessories and installed per NFPA standards.
- A standard three-year unlimited-hour limited warranty for standby applications in the U.S. And Canada. Five-year basic, five-year comprehensive, and ten-year extended limited warranties are also available.
- A standard two-year or 8700-hour limited warranty for prime power applications.
- Other features:
  - Kohler designed controllers for one-source system integration and remote communication. See Controllers on page 4.
  - The low coolant level shutdown prevents overheating (standard on radiator models only).

#### 

 Reduce operating costs, fuel consumption and greenhouse gas emissions with Conscious Care™ maintenance program.

## **General Specifications**

Orderable Generator Model Number	GMKD750
Manufacturer	Kohler
Engine: model	KD18L06
Alternator Choices	KH02970TO4D KH03450TO4D
Performance Class	Per ISO 8528-5
One Step Load Acceptance	100%
Voltage	Wye or 600 V
Controller	APM603, APM802
Fuel Tank Capacity, L (gal.)	2028-19021 (550-5025)
Fuel Consumption, L/hr (gal./hr) 100% at Standby	191 (50.5)
Fuel Consumption, L/hr (gal./hr) 100% at Prime Power	171 (45.2)
Emission Level Compliance (KDxxxx)	Tier 2
Open Unit Noise Level @ 7 m dB(A) at Rated Load	93

## **Generator Set Ratings**

				150°C Standby		130°C Standby		125°C Prime	Rise Rating	105°C Prime	
Alternator	Voltage	Ph	Hz	kW/kVA	Amps	kW/kVA	Amps	kW/kVA	Amps	kW/kVA	Amps
	120/208	3	60	750/935	2603	720/900	2499	680/850	2360	655/815	2273
	127/220	3	60	750/935	2461	750/935	2461	680/850	2231	680/850	2231
	139/240	3	60	750/935	2256	750/935	2256	680/850	2045	680/850	2045
	220/380	3	60	700/875	1330	670/835	1273	670/835	1273	610/760	1159
KH02970TO4D	230/400	3	60	725/905	1309	695/865	1254	680/850	1227	640/800	1155
	240/416	3	60	750/935	1302	720/900	1250	680/850	1180	655/815	1137
	254/440	3	60	750/935	1231	750/935	1231	680/850	1116	680/850	1116
	277/480	3	60	750/935	1128	750/935	1128	680/850	1023	680/850	1023
	347/600	3	60	750/935	903	750/935	903	680/850	818	680/850	818

RATINGS: All three-phase units are rated at 0.8 power factor. Standby Ratings: The standby rating is applicable to varying loads for the duration of a power outage. There is no overload capability for this rating. Prime Power Ratings: At varying load, the number of generator set operating hours is unlimited. A 10% overload capacity is available for one hour in twelve. Ratings are in accordance with ISO-8528-1 and ISO-3046-1. For limited running time and continuous ratings, consult the factory. Obtain technical information bulletin (TIB-101) for ratings guidelines, complete ratings definitions, and site condition derates. The generator set manufacturer reserves the right to change the design or specifications without notice and without any obligation or liability whatsoever.



## **Generator Set Ratings, continued**

				150°C Standby		130°C Standby		125°C Prime	Rise Rating	105°C Prime	
Alternator	Voltage	Ph	Hz	kW/kVA	Amps	kW/kVA	Amps	kW/kVA	Amps	kW/kVA	Amps
	120/208	3	60	750/935	2603	750/935	2603	680/850	2360	680/850	2360
	127/220	3	60	750/935	2461	750/935	2461	680/850	2231	680/850	2231
	139/240	3	60	750/935	2256	750/935	2256	680/850	2045	680/850	2045
	220/380	3	60	750/935	1425	750/935	1425	680/850	1292	680/850	1292
KH03450TO4D	230/400	3	60	750/935	1354	750/935	1354	680/850	1227	680/850	1227
	240/416	3	60	750/935	1302	750/935	1302	680/850	1180	680/850	1180
	254/440	3	60	750/935	1231	750/935	1231	680/850	1116	680/850	1116
	277/480	3	60	750/935	1128	750/935	1128	680/850	1023	680/850	1023
	347/600	3	60	750/935	903	750/935	903	680/850	818	680/850	818

Engine Specifications	60 Hz
Manufacturer	Kohler
Engine: model	KD18L06
Engine: type	4-Cycle, Turbocharged, Charge Air Cooled
Cylinder arrangement	6 Inline
Displacement, L (cu. in.)	17.960 (1096)
Bore and stroke, mm (in.)	148 x 174 (5.8 x 2.9)
Compression ratio	16.5:1
Piston speed, m/min. (ft./min.)	626 (2055)
Main bearings: quantity, type	7, Precision Half Shells
Rated rpm	1800
Max. power at rated rpm, kWm (BHP)	820 (1100)
Cylinder head material	Cast Iron
Crankshaft material	Steel
Valve (exhaust) material	Steel
Governor: type, make/model	KODEC Electronic Control
Frequency regulation, no-load to-full load	Isochronous
Frequency regulation, steady state	±0.25%
Frequency	Fixed
Air cleaner type, all models	Dry
Lubricating System	60 Hz
Туре	Full Pressure
Oil pan capacity with filter initial filling, L (qt.) $\S$	97 (102.4)
Oil filter: quantity, type §	2, Cartridge
Oil cooler	Water-Cooled

Fuel System	60 Hz
Fuel supply line, min. ID, mm (in.)	12 (0.47)
Fuel return line, min. ID, mm (in.)	8 (0.31)
Max. fuel flow, Lph (gph)	288 (76)
Min./max. fuel pressure at engine supply connection, kPa (in. Hg)	- 30/30 (- 8.8/8.8)
Max. return line restriction, kPa (in. Hg)	30 (8.9)
Fuel filter: quantity, type	1, Primary Engine Filter 1, Fuel/Water Separator

Recommended fuel

Kohler recommends the use of Kohler Genuine oil and filters.

Fuel Consumption **	(	60 Hz
Diesel, Lph (gph) at % load	Stand	lby Rating
100%	188	(49.7)
75%	151	(39.8)
50%	102	(27.0)
25%	52	(13.9)
Diesel, Lph (gph) at % load	Prim	ne Rating
100%	167	(44.2)
75%	124	(32.8)
50%	85	(22.3)
25%	47	(12.5)
** Volumetric fuel consumption is up to than #2 ULSD.	o 4% higher whe	en using HVO/

Radiator System	60 Hz
Ambient temperature, °C (°F)*	50 (122)
Radiator system capacity, including engine, L (gal.)	75.7 (20)
Engine jacket water capacity, L (gal.)	39.5 (10.4)
Engine jacket water flow, Lpm (gpm)	780 (206.1)
Charge cooler air inlet temperature at 25°C (77°F) ambient, °C (°F)	238 (460)
Heat rejected to cooling water at rated kW, dry exhaust, kW (Btu/min.)	261 (14843)
Heat rejected to charge air cooler at rated kW, dry exhaust, kW (Btu/min.)	208 (11840)
Turbocharger boost (abs) bar (psi)	3.0 (43)
Water pump type	Vane Wheel
Fan diameter, including blades, mm (in.)	1118 (44)
Fan, kWm (HP)	24 (32.2)
Max. restriction of cooling air, intake and discharge side of radiator, kPa (in. $H_2O$ )	0.125 (0.5)

\* Enclosure with enclosed silencer reduces ambient temperature capability by 5°C (9°F).

Remote Radiator System†	60 Hz
Exhaust manifold type	Dry
Water inlet/outlet, mm (in.)	76 (3)
Charge air cooler inlet/outlet (pipe dia. of flange), mm (in.)	127 (5)
Static head allowable above engine, kPa (ft. H <sub>2</sub> O)	150 (50.2)

 $<sup>\</sup>ensuremath{^\dagger}$  Contact your local distributor for cooling system options and specifications based on your specific requirements.

#2 Diesel ULSD / HVO / RD



Alternator, kW (Btu/min.)

‡ Air density =  $1.20 \text{ kg/m}^3 (0.075 \text{ lbm/ft}^3)$ 

# Industrial Diesel Generator Set - KD750 Tier 2 EPA-Certified for Stationary Emergency Applications

Exhaust System	60 Hz
Exhaust flow at rated kW, m <sup>3</sup> /min. (cfm)	135 (4757)
Exhaust temperature at rated kW at $25^{\circ}$ C ( $77^{\circ}$ F) ambient, dry exhaust, $^{\circ}$ C ( $^{\circ}$ F)	512 (954)
Maximum allowable back pressure, kPa (in. Hg)	8.5 (2.5)
Exh. outlet size at eng. hookup, mm (in.)	See ADV drawing
Electrical System	60 Hz
Battery charging alternator:	
Ground (negative/positive)	Negative
Volts (DC)	24
Ampere rating	140
Starter motor qty. at starter motor power rating, rated voltage (DC)	Standard: 1 @ 8 kW, 24
Battery, recommended cold cranking amps (CCA):	
Quantity, CCA rating each, type (with standard starter)	2, 925, WET
Battery voltage (DC)	12
Air Requirements	60 Hz
Radiator-cooled cooling air, m³/min. (scfm)‡	876 (30900)
Cooling air required for generator set when equipped with city water cooling or remote radiator, based on 14°C	
(25°F) rise, m <sup>3</sup> /min. (scfm)‡	457 (16139)
Combustion air, m <sup>3</sup> /min. (cfm)	53.1 (1875)
Heat rejected to ambient air:	
Engine, kW (Btu/min.)	90 (5123)

39 (2220)

Alternator	Specifications	60 Hz
Type		4-Pole, Rotating-Field
Exciter type	•	Brushless, Permanent- Magnet Pilot Exciter
Voltage reg	ulator	Solid-State, Volts/Hz
Insulation:		NEMA MG1, UL 1446, Vacuum Pressure Impregnated (VPI)
Materi	al	Class H, Synthetic, Nonhygroscopic
Tempe	erature rise	130°C, 150°C Standby
Bearing: qu	antity, type	1, Sealed
Coupling ty	pe	Flexible Disc
Amortisseu	r windings	Full
Alternator v	vinding type	Random Wound
Rotor balan	ncing	125%
Voltage reg	ulation, no-load to full-load	±0.25%
One-step lo	ad acceptance	100% of Rating
Unbalanced	d load capability	100% of Rated Standby Current
Peak motor starting kVA:		(35% dip for voltages below)
480 V	KH02970TO4D	2717
480 V	KH03450TO4D	3136

#### Alternator Standard Features

- The pilot-excited, permanent magnet (PM) alternator provides superior short-circuit capability.
- All models are brushless, rotating-field alternators.
- NEMA MG1, IEEE, and ANSI standards compliance for temperature rise and motor starting.
- Sustained short-circuit current of up to 300% of the rated current for up to 10 seconds.
- Sustained short-circuit current enabling downstream circuit breakers to trip without collapsing the alternator field.
- Self-ventilated and dripproof construction.
- Superior voltage waveform from two-thirds pitch windings and skewed stator.
- Brushless alternator with brushless pilot exciter for excellent load response.

**NOTE:** See TIB-102 Alternator Data Sheets for alternator application data and ratings, efficiency curves, voltage dip with motor starting curves, and short circuit decrement curves.



### **Controllers**



#### **APM802 Controller**

Provides advanced control, system monitoring, and system diagnostics for optimum performance and compatibility.

- 12-inch graphic display with touch screen and menu control provide easy local data access
- Measurements are selectable in metric or English units
- User language is selectable
- Two USB ports allow connection of a flash drive, mouse, or keypad
- Electrical data, mechanical data, and system settings can be saved to a flash drive
- Ethernet port allows connection to a PC type computer or Ethernet switch
- The controller supports Modbus® RTU and TCP protocols
- NFPA 110 Level 1 capability

Refer to G6-152 for additional controller features and accessories.

Modbus® is a registered trademark of Schneider Electric.



#### **APM603 Controller**

Provides advanced control, system monitoring, and system diagnostics for optimum performance and compatibility.

- 7-inch graphic display with touch screen and menu control provides easy local data access
- Measurements are selectable in metric or English units
- Paralleling capability to control up to 8 generators on an isolated bus with first-on logic, synchronizer, kW and kVAR load sharing, and protective relays
  - Note: Parallel with other APM603 controllers only
- Generator management to turn paralleled generators off and on as required by load demand
- Load management to connect and disconnect loads as required
- Controller supports Modbus® RTU, Modbus® TCP, SNMP and BACnet®
- Integrated voltage regulator with ±0.25% regulation
- Built-in alternator thermal overload protection
- UL-listed overcurrent protective device
- NFPA 110 Level 1 capability

Refer to G6-162 for additional controller features and accessories.

BACNet® is a registered trademark of ASHRAE.

## **Codes and Standards**

- Engine- generator set is designed and manufactured in facilities certified to ISO 9001.
- Generator set meets NEMA MG1, BS5000, ISO, DIN EN, and IEC standards, NFPA 110.
- Engine generator set is tested to ISO 8528-5 for transient response.
- The generator set and its components are prototype-tested, factory-built, and production-tested.

## Third-Party Compliance

• Tier 2 EPA-Certified for Stationary Emergency Applications

#### **Available Approvals and Listings**

- ☐ California OSHPD Pre-Approval
- ulus (UL 2200 and CSA C22.2 No.100)
- Florida Dept. Of Environmental Protection (FDEP) Compliance (fuel tank only)
- ☐ IBC Seismic Certification

## **Warranty Information**

- A standard three-year unlimited-hour limited warranty for standby applications in the U.S. And Canada. Five-year basic, five-year comprehensive, and ten-year extended limited warranties are also available.
- A standard two-year or 8700-hour limited warranty for prime power applications.

#### **Available Warranties for Standby Applications**

- ☐ 5-Year Basic Limited Warranty
- ☐ 5-Year Comprehensive Limited Warranty
- ☐ 10-Year Major Components Limited Warranty

#### Standard Features

- Closed Crankcase Ventilation (CCV) Filters
- Customer Connection
- Integral Vibration Isolation
- Local Emergency Stop Switch
- Oil Drain and Coolant Drain Extension
- Operation and Installation Literature
- Battery Rack and Cables
- Fuel/Water Separator



☐ Radiator Guard and Duct Flange

# Industrial Diesel Generator Set - KD750 Tier 2 EPA-Certified for Stationary Emergency Applications

A۷	ailable Options	
	Circuit Breakers	Electrical System
	Type Rating	☐ Battery, 2/12V, Wet
	Magnetic Trip	☐ Battery Charger
	Thermal Magnetic Trip 🔲 100%	Battery Heater; 80 W, 120 V, 1Ph
	Electronic Trip (LI) Operation	Generator Heater
	Electronic Trip with Short Time (LSI)  Manual Electrically Operated (for paralleling)	Fuel System
	Circuit Breaker Mounting	☐ Flexible Fuel Lines
_	•	Restriction Gauge (for fuel/water separator)
	Generator Mounted Remote Mounted	Literature
	Bus Bar (for remote mounted breakers)	
	Enclosed Remote Mounted Circuit Breakers	<b>Ξ</b>
_	NEMA 1 (15-5000 A)	
	NEMA 3R (15-1200 A)	☐ Overhaul
	,	· <del></del>
$\overline{\Box}$	Engine Type  KDxxxx Tier 2 EPA-Certified Engine	Miscellaneous  Air Cleaner, Heavy Duty (loose)
	KDxxxx-F Fuel Optimized Engine	Air Cleaner Restriction Indicator
		Automatic Oil Replenishment System
_	Approvals and Listings	Centrifugal Oil Filter Assembly
	California OSHPD Pre-Approval	☐ Rated Power Factor Testing
	cULus (UL 2200 and CSA C22.2 No. 100) Florida Dept. of Environmental Protection (FDEP) Compliance	Electrical Package (Requires Enclosure selection)
_	(fuel tanks only)	☐ Basic Electrical Package (select 1 Ph)
	Hurricane Rated Enclosure	☐ Wire Battery Charger (1 Ph)
	IBC Seismic Certification	☐ Wire Block Heater (select 1 Ph)
	Enclosed Unit	☐ Wire Controller Heater (1 Ph)
$\overline{\Box}$	Sound Level 1 Enclosure/Fuel Tank Package	☐ Wire Generator Heater (1 Ph)
	Sound Level 2 Enclosure/Fuel Tank Package	Warranty (Standby Applications only)
H	Sound Level 3 Enclosure/Fuel Tank Package	
_	<u> </u>	<ul><li>5-Year Basic Limited Warranty</li><li>5-Year Comprehensive Limited Warranty</li></ul>
$\overline{}$	Open Unit	10-Year Major Components Limited Warranty
Ч	Exhaust Silencer, Critical (kits: PA-354894 qty. 1)	Other
	Exhaust Silencer, Hospital (kits: PA-354907 qty. 1)	
	Exhaust Silencer, Residential (kits: PA-354992 qty. 1)	<u> </u>
	Flexible Exhaust Connector, Stainless Steel	
	Controller	
	Input/Output, Digital	
	Load Shed (APM802 only)	Dimensions and Weights
	Manual Key Switch	Overall Size, max., L x W x H, mm (in.): 3600 x 1900 x 2151
	Remote Emergency Stop Switch	(141.7 x 74.8 x 84.7)
	Lockable Emergency Stop Switch	Weight, radiator model, max. wet, kg (lb.): 5840 (12875)
	Remote Serial Annunciator Panel	
	Cooling System	
	Block Heater; 3000 W, 208 V, (select 1 Ph) *	
	Block Heater; 3250 W, 240 V, (select 1 Ph) *	
	Block Heater; 3000 W, 480 V, (select 1 Ph) *  * Required for ambient temperatures below 10°C (50°F).  Block heater kit includes air intake manifold grid heater.	

- w-



KOHLER CO., Kohler, Wisconsin 53044 USA Phone 920-457-4441, Fax 920-459-1646 For the nearest sales and service outlet in the US and Canada, phone 1-800-544-2444 KOHLERPower.com

### Sound Enclosures and Subbase Fuel Tank

#### Sound Level 1 Enclosure Standard Features

- Internal silencers with flexible exhaust connectors and exhaust elbows.
- Optional subbase fuel tank.
- Fade-, scratch-, and corrosion-resistant Kohler<sup>®</sup>
   Power Armor<sup>™</sup> automotive-grade textured finish.
- Acoustic insulation that meets UL 94 HF1 flammability classification.
- Aluminum construction with large access doors that are hinged for easy maintenance.
- Lockable, flush-mounted door latches.
- Air inlet louvers reduce rain and snow entry.
- Vertical outlet hood with 90 degree angles to redirect air and reduce noise.
- Sound level 1 enclosure is designed to 150 mph (241 kph) wind load rating.

#### Sound Level 2 Enclosure Standard Features


- Includes all of the sound level 1 enclosure features with the addition of up to 51 mm (2 in.) acoustic insulation material, intake sound baffles, vertical air discharge, and secondary silencers.
- Sound level 2 enclosure is certified to 200 mph (322 kph) wind load rating.

#### Sound Level 3 Enclosure Standard Features


- Includes all of the sound level 1 and 2 enclosure features.
- Sound level 3 enclosure has extended intake baffles, extended discharge with sound baffles.

#### Subbase Fuel Tank Features


- The fuel tank has a Power Armor Plus<sup>™</sup> textured epoxy-based rubberized coating.
- The above-ground rectangular secondary containment tank mounts directly to the generator set, below the generator set skid (subbase).
- Both the inner and outer tanks have UL-listed emergency relief vents.
- Flexible fuel lines are provided with subbase fuel tank selection.
- The containment tank's construction protects against fuel leaks or ruptures. The inner (primary) tank is sealed inside the outer (secondary) tank. The outer tank contains the fuel if the inner tank leaks or ruptures.
- The above ground secondary containment subbase fuel tank meets UL 142 requirements.
- State tanks with varying capacities are available.
   Florida Dept. Of Environmental Protection (FDEP)
   File No. EQ-634 approved.



Sound Level 1 and 2 Enclosure



Sound Level 3 Enclosure



Subbase Fuel Tank (Top View)

DISTRIBUTED BY: