

PRODUCT GUIDE

For Marine Generators



KOHLER[®]
IN POWER. SINCE 1920.


ALWAYS PRESENT NEVER NOTICED



KOHLER® marine generators are smaller. Quieter. With less vibration.* Each one is built to last and designed to go unnoticed.

Enjoy the journey.

*Compared to previous KOHLER generator models.



WHY KOHLER

PROVEN RELIABILITY

Every KOHLER generator is extensively quality-tested—before model release and before leaving the factory. The result is proven reliability.

PREMIUM LIMITED WARRANTY

Enjoy full protection throughout the duration of our industry-leading warranty.

GLOBAL SUPPORT

With nearly 1000 sales and service locations around the world, we're everywhere you go.

Information, specifications, materials and dimensions are subject to change without notice.



DIESEL GENERATORS

Equipped with either an Advanced Digital Control IId (5 to 11-kW units) or Decision-Maker® Controller (12 to 200 kW) and the industry's most acoustically advanced sound shields, KOHLER® diesel generators provide the ultimate in overall performance.

Standard Features

- Remote start connection availability
- Class H insulation
- Multivoltage adjustability
- Voltage regulation of $\pm 1-2\%$
- Frequency regulation $\pm 5\%$ droop, .8% steady state for mechanically governed models, .5% isochronous for electronically governed models
- Radio suppression

Optional Accessories

- Remote start and meter panel kit
- Siphon break
- Remote digital gauge
- Sound shield (depending on model)



55-kW generator with DEC 3500 Controller

Information, specifications, materials and dimensions are subject to change without notice.

DIESEL GENERATORS

Model	kW*	Hz	Cyl	RPM	Ph	Voltage	Amps	Length x Width x Height mm (in) H – Housed / U – Unhoused	Weight (Wet) kg (lb)
6EKOD	6	60	3	1800	1	120	50	H – 780 (30.7) x 528 (20.8) x 559 (22) U – 743 (29.3) x 448 (17.6) x 536 (21.1)	H – 222 (489) U – 185 (407)
						120 / 240	50 / 25		
5EFKOD	5	50	3	1500	1	115 / 230	43.4 / 21.7	H – 865 (34.1) x 528 (20.8) x 559 (22) U – 827 (32.6) x 448 (17.6) x 536 (21.1)	H – 249 (548) U – 211 (465)
						230	21.7		
						240	20.8		
9EKOZD	8.5	60	3	1800	1	120	70.8	H – 960 (37.8) x 528 (20.8) x 559 (22) U – 922 (36.3) x 448 (17.6) x 536 (21.1)	H – 279 (616) U – 241 (532)
						120 / 240	70.8 / 35.4		
7EFKOZD	7	50	3	1500	1	115 / 230	60.8 / 30.4	H – 960 (37.8) x 528 (20.8) x 559 (22) U – 922 (36.3) x 448 (17.6) x 536 (21.1)	H – 406 (896) U – 376 (830)
						230	30.4		
						240	29.2		
11EKOZD	11	60	4	1800	1	120	91.7	H – 1064 (41.9) x 652.5 (25.7) x 711 (27.9) U – 984 (38.8) x 580 (22.8) x 695 (27.4)	H – 395 (870) U – 376 (830)
						120 / 240	91.7 / 45.8		
9EFKOZD	9	50	4	1500	1	115 / 230	78.3 / 39.1	H – 1064 (41.9) x 652.5 (25.7) x 711 (27.9) U – 984 (38.8) x 580 (22.8) x 695 (27.4)	H – 395 (870) U – 376 (830)
						230	39.1		
						240	37.5		
11EKOZD	11	60	4	1800	3	220 / 380	20.9	H – 1064 (41.9) x 652.5 (25.7) x 711 (27.9) U – 984 (38.8) x 580 (22.8) x 695 (27.4)	H – 395 (870) U – 376 (830)
						240 / 416	19.1		
9EFKOZD	9	50	4	1500	3	120 / 240	33.1	H – 1064 (41.9) x 652.5 (25.7) x 711 (27.9) U – 984 (38.8) x 580 (22.8) x 695 (27.4)	H – 395 (870) U – 376 (830)
						127 / 220	36.1		
						230 / 400	16.2		
14EKOZD	14	60	3	1800	1	120	117	H – 1064 (41.9) x 652.5 (25.7) x 711 (27.9) U – 984 (38.8) x 580 (22.8) x 695 (27.4)	H – 395 (870) U – 376 (830)
						120 / 240	59		
12EFKOZD	12	50	3	1500	1	230	53	H – 1064 (41.9) x 652.5 (25.7) x 711 (27.9) U – 984 (38.8) x 580 (22.8) x 695 (27.4)	H – 395 (870) U – 376 (830)
						240	40		

*kW rating varies by voltage. Consult the generator spec sheet for more detail.

Information, specifications, materials and dimensions are subject to change without notice.

DIESEL GENERATORS

Model	kW*	Hz	Cyl	RPM	Ph	Voltage	Amps	Length x Width x Height mm (in) H – Housed / U – Unhoused	Weight (Wet) kg (lb)
14EKOZD	14	60	3	1800	3	120 / 208	49	H – 1064 (41.9) x 652.5 (25.7) x 711 (27.9) U – 984 (38.8) x 580 (22.8) x 695 (27.4)	H – 406 (896) U – 376 (830)
						120 / 240	43		
						120 / 240	59		
						127 / 220	46		
						139 / 240	43		
277 / 480	22								
12EFKOZD	12	50	3	1500	3	110 / 190	46		
						115 / 230	38		
						115 / 230	53		
						120 / 208	42		
						230 / 400	22		
16EKOZD	16	60	3	1800	1	240 / 416	21		
						220 / 380	23		
						120	134		
13.5EFKOZD	14	50	3	1500	1	120 / 240	67		
						230	59		
						240	40		
16EKOZD	16	60	3	1800	3	120 / 208	56	H – 1064 (41.9) x 652.5 (25.7) x 711 (27.9) U – 1003 (39.5) x 580 (22.8) x 695 (27.4)	H – 395 (870) U – 376 (830)
						120 / 240	49		
						120 / 240	67		
						127 / 220	53		
						139 / 240	49		
277 / 480	25								
13.5EFKOZD	13.5	50	3	1500	3	110 / 190	52		
						115 / 230	43		
						115 / 230	59		
						120 / 208	47		
						230 / 400	25		
						240 / 416	24		
						220 / 380	26		

Model	kW*	Hz	Cyl	RPM	Ph	Voltage	Amps	Length x Width x Height mm (in) H – Housed / U – Unhoused	Weight (Wet) kg (lb)	
21EKOZD	21 / 21	60	4	1800	1	120	175	H – 1197 (47.12) x 652.5 (25.69) x 711(27.99) U – 1121 (44.13) x 577.5 (22.74) x 694(27.31)	H – 480 (1059) U – 440 (970)	
	21 / 21					120 / 240	88			
18EFKOZD	18 / 18	50		1500		1	230			79
	14.5 / 14.5						240			61
21EKOZD	21	60	4	1800	3	120 / 208	73			
						120 / 240	64			
						120 / 240	80			
						127 / 220	69			
						139 / 240	64			
17EFKOZD	17	50	4	1500	3	277 / 480	32			
						110 / 190	65			
						115 / 230	54			
						115 / 230	70			
						120 / 208	58			
24EKOZD	24	60	4	1800	1	230 / 400	31			
						240 / 416	29			
						220 / 380	33			
20.5EFKOZD	21	50	4	1500	1	120	200			
						120 / 240	100			
						230	90			
						240	78			

DIESEL GENERATORS

Model	kW*	Hz	Cyl	RPM	Ph	Voltage	Amps	Length x Width x Height mm (in) H – Housed / U – Unhoused	Weight (Wet) kg (lb)							
24EKOZD	24	60	4	1800	3	120 / 208	84	H – 1197 (47.1) x 652.5 (25.7) x 711 (27.9) U – 1138 (44.8) x 577.5 (22.7) x 694 (27.3)	H – 489 (1078) U – 449 (990)							
						120 / 240	73									
					1	120 / 240	92									
						127 / 220	79									
						139 / 240	73									
20.5EFKOZD	20.5	50	4	1500	3	277 / 480	37									
						110 / 190	78									
					1	115 / 230	65									
						115 / 230	85									
						120 / 208	72									
32EKOZD	32	60	4	1800	3	230 / 400	37	H – 1303 (51.30) x 661 (26.04) x 778 (30.64) U – 1222 (48.13) x 643 (25.33) x 733 (28.86)	H – 607 (1339) U – 531 (1170)							
						240 / 416	36									
					1	220 / 380	39									
						120 / 240	133									
						120 / 208	111									
28EFKOZD	28	50	4	1500	3	120 / 240	96									
						120 / 240	142									
					1	127 / 220	105									
						139 / 240	96									
						277 / 480	48									
32EKOZD	32	60	4	1800	3	120 / 240	96	H – 1303 (51.30) x 661 (26.04) x 778 (30.64) U – 1222 (48.13) x 643 (25.33) x 733 (28.86)	H – 607 (1339) U – 531 (1170)							
						120 / 240	142									
					1	127 / 220	105									
						139 / 240	96									
						277 / 480	48									
					28EFKOZD	28	50			4	1500	3	110 / 190	106	H – 1303 (51.30) x 661 (26.04) x 778 (30.64) U – 1222 (48.13) x 643 (25.33) x 733 (28.86)	H – 607 (1339) U – 531 (1170)
													110 / 220	92		
												1	115 / 230	117		
													120 / 208	97		
													230 / 400	51		
32EKOZD	32	60	4	1800				3	230 / 400			51	H – 1303 (51.30) x 661 (26.04) x 778 (30.64) U – 1222 (48.13) x 643 (25.33) x 733 (28.86)	H – 607 (1339) U – 531 (1170)		
									240 / 416			49				
								1	220 / 380			53				
									120 / 240			133				
									120 / 208			111				

Model	kW*	Hz	Cyl	RPM	Ph	Voltage	Amps	Length x Width x Height mm (in) H – Housed / U – Unhoused / R – Radiator	Weight (Wet) kg (lb)							
40EKOZD	40	60	4	1800	3	120 / 240	152	H – 1354 (53.31) x 661 (26.04) x 778 (30.64) U – 1274 (50.17) x 643 (25.33) x 733 (28.86)	H – 637 (1404) U – 567 (1250)							
						120 / 208	139									
					1	120 / 240	120									
						120 / 240	142									
						127 / 220	131									
						139 / 240	120									
35EFKOZD	35	50	4	1500	3	277 / 480	60			H – 1354 (53.31) x 661 (26.04) x 778 (30.64) U – 1274 (50.17) x 643 (25.33) x 733 (28.86)	H – 637 (1404) U – 567 (1250)					
						110 / 190	129									
					1	110 / 220	112									
						115 / 230	130									
						120 / 208	121									
					33EFOZDJ	33	50					4	1500	3	230 / 400	63
								240 / 416	61							
								1	220 / 380					65		
									110 / 190					125		
									110 / 220					108		
33EFOZDJ	33	50	4	1500	3	115 / 230	143	H – 1633 (64.3) x 767 (30.2) x 1015 (39.9) U – 1524 (60) x 722 (28.4) x 960 (37.8) R – 1858 (73.2) x 827 (32.6) x 1265 (49.8)	H – 1025 (2260) U – 935 (2060) R – 957 (2110)*							
						220 / 380	63									
					1	230 / 400	60									
						110 / 190	125									
						110 / 220	108									
33EFOZDJ	33	50	4	1500	3	240 / 416	57			H – 1633 (64.3) x 767 (30.2) x 1015 (39.9) U – 1524 (60) x 722 (28.4) x 960 (37.8) R – 1858 (73.2) x 827 (32.6) x 1265 (49.8)	H – 1025 (2260) U – 935 (2060) R – 957 (2110)*					
						240 / 416	57									
					1	230 / 400	60									
						110 / 190	125									
						110 / 220	108									

DIESEL GENERATORS

Model	kW*	Hz	Cyl	RPM	Ph	Voltage	Amps	Length x Width x Height mm (in)		Weight (Wet) kg (lb)	
								H – Housed / U – Unhoused / R – Radiator			
40EFOZDJ	40	50	4	1500	3	110 / 190	152	H – 1633 (64.3) x 767 (30.2) x 1015 (39.9) U – 1549 (60.9) x 738 (29) x 961 (37.8) R – 1884 (74.2) x 827 (32.5) x 1265 (49.8)		H – 1080 (2380) U – 971 (2140) R – 993 (2190)*	
						110 / 220	131				
						1	115 / 230 220 / 380				174 76
						3	230 / 400 240 / 416				72 69
50EFOZDJ	50	50	4	1500	3	110 / 190	190	H – 1690 (66.5) x 767 (30.2) x 1015 (39.9) U – 1606 (63.2) x 738 (29) x 961 (37.8) R – 1941 (76.4) x 827 (32.5) x 1265 (49.8)		H – 1114 (2456) U – 1005 (2216) R – 1028 (2266)*	
						1	115 / 230 220 / 380				196 95
						3	230 / 400 240 / 416				90 87
						3	120 / 208 120 / 240				191 165
55EFOZDJ	55	60	4	1800	3	120 / 240	221	H – 1633 (64.3) x 767 (30.2) x 1015 (39.9) U – 1549 (60.9) x 738 (29) x 961 (37.8) R – 1884 (74.2) x 827 (32.5) x 1265 (49.8)		H – 1090 (2404) U – 982 (2164) R – 1004 (2214)*	
						1	127 / 220 139 / 240				180 165
						3	277 / 480 110 / 190				83 171
						3	110 / 220 115 / 230				148 196
45EFOZDJ	45	50	4	1500	3	220 / 380	86				
						1	220 / 380 230 / 400				86 79
						3	230 / 400 240 / 416				79 71
						3	120 / 208 120 / 240				191 165

Model	kW*	Hz	Cyl	RPM	Ph	Voltage	Amps	Length x Width x Height mm (in)		Weight (Wet) kg (lb)	
								H – Housed / U – Unhoused / R – Radiator			
65EFOZDJ	65	60	4	1800	3	120 / 208	226	H – 1690 (66.5) x 767 (30.2) x 1015 (39.9) U – 1606 (63.2) x 738 (29) x 961 (37.8) R – 1941 (76.4) x 827 (32.5) x 1265 (49.8)		H – 1125 (2480) U – 1016 (2240) R – 1039 (2290)*	
						1	120 / 240 127 / 220				221 213
						3	139 / 240 277 / 480				195 98
						3	110 / 190 110 / 220				209 181
55EFOZDJ	55	50	4	1500	3	115 / 230	217				
						1	115 / 230 220 / 380				217 105
						3	230 / 400 240 / 416				95 89
						3	120 / 208 120 / 240				278 241
80EFOZDJ	80	60	4	1800	3	127 / 220	262	H – 1754 (69) x 831 (32.7) x 1032 (40.6) U – 1657 (65.2) x 753 (29.6) x 999 (39.3) R – 1992 (78.4) x 890 (35) x 1277 (50.2)		H – 1270 (2800) U – 1148 (2530) R – 1179 (2600)*	
						1	139 / 240 277 / 480				241 120
						3	110 / 190 110 / 220				266 230
						3	220 / 380 230 / 400				133 126
70EFOZDJ	70	50	4	1500	3	240 / 416	121				
						3	240 / 416				121

DIESEL GENERATORS

Model	kW*	Hz	Cyl	RPM	Ph	Voltage	Amps	Length x Width x Height mm (in) H – Housed / U – Unhoused / R – Radiator	Weight (Wet) kg (lb)
99EOZDJ	99	60	4	1800	3	120 / 208	343	H – 1829 (72) x 831 (32.7) x 1032 (40.6) U – 1732 (68.2) x 753 (29.6) x 999 (39.3) R – 2067 (81.3) x 890 (35) x 1277 (50.2)	H – 1356 (2990) U – 1243 (2740) R – 1275 (2810)
						120 / 240	298		
						127 / 220	325		
						139 / 240	298		
						277 / 480	149		
80EFOZDJ	80	50	4	1500	3	110 / 190	304		
						110 / 220	262		
						220 / 380	152		
						230 / 400	144		
						240 / 416	139		
125EOZDJ	125	60	6	1800	3	120 / 208	434	H – 2205 (86.8) x 971 (38.2) x 1065 (41.9) U – 2068 (81.4) x 893 (35.2) x 1003 (39.5) R – 2466 (97.1) x 1129 (44.5) x 1275 (50.2)	H – 1683 (3710) U – 1515 (3340) R – 1578 (3478)
						120 / 240	376		
						127 / 220	410		
						139 / 240	376		
						277 / 480	188		
100EFOZDJ	100	50	6	1500	3	110 / 190	380		
						120 / 208	347		
						110 / 220	328		
						220 / 380	190		
						230 / 400	180		
						240 / 416	173		

Model	kW*	Hz	Cyl	RPM	Ph	Voltage	Amps	Length x Width x Height mm (in) H – Housed / U – Unhoused / R – Radiator	Weight (Wet) kg (lb)
150EOZDJ	150	60	6	1800	3	120 / 208	520	H – 2205 (86.8) x 971 (38.2) x 1065 (41.9) U – 2091 (82.3) x 893 (35.2) x 1003 (39.5) R – 2498 (98) x 1129 (44.5) x 1275 (50.2)	H – 1719 (3789) U – 1551 (3419) R – 1613 (3557)
						120 / 240	451		
						127 / 220	492		
						139 / 240	451		
						277 / 480	226		
125EFOZDJ	125	50	6	1500	3	120 / 208	433		
						110 / 220	409		
						220 / 380	237		
						230 / 400	225		
						240 / 416	217		
200EOZDJ	200	60	6	1800	3	120 / 208	694	H – 2661 (104.8) x 1048 (41.3) x 1174 (46.2) U – 2490 (98) x 970 (38.2) x 1086 (42.8)	H – 2147 (4733) U – 2067 (4558)
						120 / 240	601		
						127 / 220	656		
						139 / 240	601		
						277 / 480	301		
175EFOZDJ	175	50	6	1500	3	110 / 190	665		
						110 / 220	574		
						120 / 208	607		
						220 / 380	332		
						230 / 400	316		
						240 / 416	304		



GLOBAL SUPPORT

With nearly 1000 sales and service locations all over the world, we're everywhere you go.

AMERICAS CARIBBEAN

+1 920 565 3381
+1 800 544 2444
FAX +1 920 459 1646

CHINA

+86 21 26062169
+86 400 1808 900

EUROPE MIDDLE EAST AFRICA

+31 168 331630
FAX +31 168 331631

ASIA PACIFIC

+65 6660 2681
FAX +65 6264 6455

NEW ZEALAND AUSTRALIA

+61 88 29 02100

INDIA

+91 80 42867000
FAX +91 80 23615972



KOHLERPOWER.COM

Printed in U.S.A. G12-480 06/18 © 2018 by Kohler Co.

KOHLER
IN POWER. SINCE 1920.