

# GENERATORS

Portable Full Line



**KOHLER**<sup>®</sup>  
IN POWER. SINCE 1920.

# TOUGH AS NAILS AND LOADED WITH MUSCLE.

Whether you're camping, working in the middle of nowhere or backing up your home during an outage, we give you the power you need where you need it most. Choose generator models from 1.8 to 12.3 kW, pumps from two to four inches and our U-Spec. custom accessory system that lets you customize your equipment any way you want.

## WHY KOHLER?



From left to right:  
enCUBE® battery inverter with 60-watt solar panel  
PRO9.OE with wheel, leg and wheelbarrow handle kits

### RELIABILITY

KOHLER® power equipment is extensively quality-tested before model release and before leaving the factory—for proven reliability.

### LONG RUNTIMES

Big fuel tanks mean long runtimes and less refueling.

### ROCK-SOLID ENGINES

KOHLER engines are built to perform in the toughest environments—from the die-hard KOHLER Command PRO® to the ultra fuel-efficient Command PRO EFI.

Auto-idle feature automatically sets the engine to idle to save fuel.

### U-SPEC. CUSTOM ACCESSORY SYSTEM

U-Spec lets you build your equipment just the way you want it.

Legs, handles, wheels, lifting kits and more add up to more than 100 custom configurations.



### FREE LOANER PROGRAM

If a KOHLER generator ever goes down, one of our select dealers will provide a free loaner unit for warranty repairs exceeding 24 hours.\*

### LONG WARRANTY

You get our three-year limited warranty.†

### PROTECTIVE FEATURES

Automatic voltage regulation keeps power output clean to run equipment safely.

Ground-fault circuit interrupter protects equipment from faulty current.

Accu-Fill® provides safe, easy refilling—and less spilling—with its angled fuel inlet.

Maintenance Minder displays hours of runtime and lights up to remind you of oil, spark plug and filter changes.

### ONE GENERATOR. THREE FUEL OPTIONS.

Chose your fuel source—gasoline, propane or natural gas for ultimate flexibility and convenience.‡

### TRUSTED WORLDWIDE

Since 1920, hospitals, airports and military bases around the world have depended on KOHLER generators.

\*On PRO generator models at participating dealers, based on availability.  
†90-day limited warranty on the enCUBE1.8 and GEN5.0 when used in a commercial setting.  
‡Available on 6.4 kW generator models.

# HOW PORTABLE GENERATORS WORK WHEN THE POWER GOES OUT.

Portable Generator with Manual Transfer Switch	Portable Generator with Extension Cords
<b>BEFORE THE POWER GOES OUT</b>	
A professional will install a manual transfer switch and power inlet box to back up hardwired items and critical circuits.	Ensure you have outdoor-rated extension cords, fuel and a well-ventilated location far from windows, doors and vents in the event of an outage.
<b>WHEN THE POWER FAILS</b>	
Move your portable generator at least 10 feet away from the outdoor power inlet box in a well-ventilated location. Add fuel to the generator.*	Move your portable generator outdoors to a well-ventilated outdoor location. Add fuel to the generator.
Plug your portable generator into the power inlet box, start the generator and flip the switch—no extension cords necessary.	Safely run outdoor-rated extension cords from the generator to the appliances you want to power.
<b>WHEN UTILITY POWER IS RESTORED</b>	
Flip the switch back to utility power, shut down the generator and disconnect the power cord.	Power down the generator and disconnect the extension cords.
Store generator properly when not in use.	Store generator properly when not in use.



## Alternative Energy Back-Up Power

With no engine or need for fuel, enCUBE battery inverter is a clean power source with zero emissions, which means it can be used indoors. It charges through a 120-V AC wall outlet or optional solar panel (sold separately) and is perfect for camping, tailgating or temporary outages at home. Built-in wheels and telescopic handles make it incredibly portable.



enCUBE battery inverter with 60-watt solar panel

## PORTABLE GENERATORS

MODEL	INVERTER	GENERATORS				
		GEN5.0	PR06.4	PR06.4E	PR09.0	PR09.0E
DESCRIPTION	1.8-kW Battery inverter	5-kW Recreational home generator	6.4-kW Professional generator	6.4-kW Professional e-start generator	9.0-kW Professional generator	9.0-kW Professional e-start generator
MAX POWER (watts)	1800	5000	6400	6400	9000	9000
CONTINUOUS POWER (watts)	1440	4300	5200	5200	7200	7200
STARTING TYPE	Power Button	Recoil	Recoil	Electric + Recoil	Recoil	Electric + Recoil
ENGINE DISPLACEMENT (cu in/cc)	NA	16.9 / 277	16.9 / 277	16.9 / 277	26.2 / 429	26.2 / 429
FUEL TYPE	Solar	Gasoline	Gasoline	Gasoline	Gasoline	Gasoline
FUEL TANK CAPACITY (gal/l)	NA	8.0 / 30.2	8.0 / 30.2	8.0 / 30.2	8.0 / 30.2	8.0 / 30.2
RUNTIME AT 50% LOAD (hrs)	Varies based on equipment	16.5	15	15	11	11
DRY WEIGHT (lb/kg)	109 / 49.4	180 / 82	174 / 79	198 / 90	202 / 92	218 / 99
DIMENSIONS L x W x H (in/mm)	11.5 x 14.0 x 22.0 (292 x 356 x 559)	29.4 x 21.4 x 22.3 (746 x 543 x 566)	29.4 x 21.4 x 22.3 (746 x 543 x 566)	29.4 x 21.4 x 22.3 (746 x 543 x 566)	29.4 x 21.4 x 22.3 (746 x 543 x 566)	29.4 x 21.4 x 22.3 (746 x 543 x 566)
⚠ 120 V 15 AMP	2					
⚠ NEMA 5-20 120 V (20 AMP)		4	4	4	4	4
⚠ NEMA L5-30 120 V (30 AMP)			1	1	1	1
⚠ NEMA L14-20 120/240 V (20 AMP)		1				
⚠ NEMA L14-30 120/240 V (30 AMP)			1	1	1	1
⚠ TWIST-LOCK 120/240 V (50 AMP)						
⚠ 12 VDC (8.3 AMP)				1		1
⚠ 5V DC USB PORTS	2					
⚠ 12 V CAR CHARGER	2					
AUTO-IDLE DOWN				•		•
ACCU-FILL		•	•	•	•	•
MAINTENANCE MINDER			•	•	•	•
LOW-OIL SHUTDOWN (Oil Sentry™)		•	•	•	•	•
COMMERCIAL / CONSUMER WARRANTY	90 days / 3 yr	90 days / 3 yr	3 yr / 3 yr	3 yr / 3 yr	3 yr / 3 yr	3 yr / 3 yr
COMPLIANCE	EPA / CARB / CSA	EPA / CARB / CSA	EPA / CARB / CSA / OSHA	EPA / CARB / CSA / OSHA	EPA / CARB / CSA / OSHA	EPA / CARB / CSA / OSHA

# PUMPS

MODEL	WATER PUMPS		TRASH PUMPS	
	WP2.0	WP3.0	TP3.0	TP4.0D
DESCRIPTION	2-inch water pump	3-inch water pump	3-inch trash pump	4-inch diesel trash pump
ENGINE DISPLACEMENT (cu in/cc)	12.7 / 208	12.7 / 208	16.9 / 277	21.3 / 349
FUEL TYPE	Gasoline	Gasoline	Gasoline	Diesel
FUEL TANK CAPACITY (gal/L)	1.1 / 4.1	1.1 / 4.1	1.8 / 6.8	1.1 / 4.1
TOTAL HEAD (ft/m)	85 / 25.9	98 / 29.8	85 / 26	50 / 15.2
SUCTION HEAD (ft/m)	26 / 7.9	26 / 7.9	26 / 7.9	26 / 7.9
FLOW RATE (gpm/lpm)	159 / 601	265 / 1003	317 / 1200	395 / 1495
IMPELLER	Cast Iron	Cast Iron	Cast Iron	Cast Iron
VOLUTE	Cast Iron	Cast Iron	Cast Iron	Cast Iron
PUMP BODY	Aluminum	Aluminum	Aluminum	Cast Iron
DRY WEIGHT (lb/kg)	66 / 29.9	77 / 34.9	137 / 62.1	198 / 89.8
DIMENSIONS L x W x H (in/mm)	24.2 x 18.7 x 19.0 (614 x 475 x 482)	24.2 x 18.7 x 19.0 (614 x 475 x 482)	27.0 x 20.9 x 21.3 (685 x 530 x 541)	28.7 x 22.8 x 23.4 (728 x 579 x 594)
COMMERCIAL/CONSUMER WARRANTY (yrs)	3 yr / 3 yr			



# U-SPEC® CUSTOM ACCESSORY SYSTEM

	PORTABLE GENERATORS					PUMPS			
	GEN5.0	PRO6.4	PRO6.4E	PRO9.0	PRO9.0E	WP2.0	WP3.0	TP3.0	TP4.0D
A. LIFTING KIT	•	•	•	•	•				
B. AUTO-LOCKING HAND TRUCK HANDLE KITS	•	•	•	•	•				
C. WHEELBARROW HANDLE KIT	*	*	*	*	*	•	•	•	
D. EXTENSION CORD MANAGEMENT KIT	•	•	•	•	•	•	•	•	
E. LEG KIT	*	*	*	*	*	•	•	•	
F. WHEEL KIT	*	*	*	*	*	•	•	•	
G. 12-V BATTERY CHARGER			•		•				
H. HOSE KIT						•	•	•	•
I. ISOLATOR KIT	•	•	•	•	•	•	•	•	
J. MOBILITY KITS	•								•
K. TRI-FUEL KITS		•	•						
L. WIRELESS REMOTE									

Not pictured below: G through L  
\*Standard features available on all -3002 models

## CUSTOM OPTIONS—AND LOTS OF THEM.

We know every job and every job site is different. That's why we offer the U-Spec® custom accessory system. It lets you build your generator or pump just the way you want it, with more custom configurations than anyone else.



## THE BENEFITS OF TRI-FUEL KITS:



## ULTIMATE FLEXIBILITY AND CONVENIENCE

Choose your fuel source—gasoline, propane or natural gas. When plugged into your home's natural gas or propane line, you never need to refuel.

## FULL WARRANTY SUPPORT

When installed by an authorized KOHLER dealer, the Tri-Fuel Kit keeps your generator warranty intact, unlike aftermarket kits, which void your warranty.

## EARTH-FRIENDLY

Propane is odorless and nontoxic. Clean-burning natural gas and propane cost less than gasoline and help reduce harmful carbon emissions.

**KOHLER**<sup>®</sup>  
IN POWER. SINCE 1920.

**North America** 800.544.2444

**KOHLERPOWER.COM**

PRINTED IN U.S.A. 27451-01 G12-452 2/21 ©2021 BY KOHLER CO.