

Touchless single-hole lavatory faucet with Kinesis® sensor technology, DC-powered, 0.5 gpm K-104S36-SANA

Features

- Kinesis[®] technology with concealed sensor allows for a clean aesthetic and provides extraordinarily accurate and reliable actuation in varying installation environments
- Below-counter valving reduces the faucet footprint and provides easier service
- Design-forward aesthetic for commercial bathroom spaces
- 0.5 gpm (1.9 lpm) maximum flow rate
- AA battery-powered; up to four-year battery life (approx. 105,000 cycles)
- On-demand usage with 30-second max. continual run cycle to prevent vandalism and save water
- Vandal-resistant aerator
- 18" (457 mm) stainless steel braided flexible supply hose for easy installation
- 5-1/4" (133 mm) spout reach
- Grid drain
- Concealed mechanical mixer sold separately
- Complies with the Safe Drinking Water Act (SDWA)
- Includes spout assembly, grid drain, control box assembly, supply hose, and standard mounting hardware
- Includes four AA batteries

Material

- Metal construction spout
- Cast brass valve

Technology

 Kinesis[®] sensor technology offers on-demand detection for maximum water savings

Installation

Single-hole mounting

Recommended Products/Accessories

K-23726 Drain treatment K-23723 Faucet cleaner

Optional Products/Accessories

K-99799 Thermostatic Tempering Valve K-13478-A 4" escutcheon plate for Insight[™] and Kinesis® faucet

K-13478-B 4" escutcheon plate for $\mathsf{Insight}^{\mathsf{TM}}$ and $\mathsf{Kinesis}^{\mathbb{R}}$ faucet

K-13479-A 8" escutcheon plate for Insight[™] and Kinesis® faucet

K-13479-B 8" escutcheon plate for Insight[™] and Kinesis[®] faucet

Included Components

1-800-4KOHLER (1-800-456-4537) Kohler Co. reserves the right to make revisions without notice to product specifications. For the most current Specification Sheet, go to <u>www.kohler.com</u> USA or <u>www.kohler.ca</u> Canada 3-23-2024 19:32 - US





Codes/Standards

ASME A112.18.1/CSA B125.1 NSF/ANSI/CAN 61 NSF/ANSI/CAN 372 All applicable US Federal and State material regulations DOE - Energy Policy Act 1992 California Energy Commission (CEC) ADA ICC/ANSI A117.1 CSA B651 OBC IAPMO Certification

KOHLER[®] One-Year Limited

Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description




CP Polished Chrome



Strayt™

KOHLER, Faucets

Strayt™ Touchless single-hole lavatory faucet with Kinesis® sensor technology, DC-powered, 0.5 gpm K-104S36-SANA



Technical Information

All product dimensions are nominal.

Power source: Battery - DC, included

Faucet:

Flow rate: 0.5 gal/min (1.9 l/min) Pressure: 60 psi (4.1 bar)

Drain included:

Spout:

Yes

5-1/4" (133 mm)

Spout reach:

Notes

Install this product according to the installation instructions.

A 1-1/4" (32 mm) minimum to 1-1/2" (38 mm) maximum diameter mounting hole is required. The minimum distance between the back of the faucet spout and the wall must be 1-3/4" (44 mm). This will allow proper clearance for setscrew access.

The maximum distance between the bathroom sink basin edge to the base of the faucet spout must be 1-3/4" (44 mm).

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

